
Panel-mount Socket LB-IF2R

Insulated, Ø 2 mm with spring-loaded MULTILAM. Machined brass. Metal thread jacket on the insulation. The socket can be screw-mounted in predrilled panels.

Flat connecting tab 2.8 mm x 0.8 mm.





Order No.	Туре	Rated voltage/current		*Colors
23.0060-*	LB-IF2R	30 VAC / 10 A 60 VDC / 10 A	Opt	20 21 22 23 24 25 26 27 28 29

Component parts

23.5021-*	BI-LB-IF2R	Socket
Page 68	MU/M6x0,5	Hexagon nut
Page 69	SP2	Washer