
## Plug SLS425-SE...

Stackable, Ø 4 mm, with spring-loaded MULTILAM, for self-assembly of test leads. With rigid insulating sleeve. Nickel-plated and gold-plated versions available.

## Various types of connection:

SLS425-SE/M: Screw connection







Order No.	Туре	Rated voltage/current	Cable (A)			*Colors
22.2656-*	SLS425-SE/M	1000 V, CAT II / 32 A 600 V, CAT III / 32 A	~ Ø 3,9 mm	0,75 2,5 mm²	Au	20 21 22 23 24   25 26 27 28 29

## **Component parts**

22.2380-*	KT425-SE	Insulator (*Colors see: SLS425-SE/M)	
22.1027	LS425-SE/M	Plug suitable for: SLS425-SE/M	



Assembly instructions MA161

www.staubli.com/electrical