



6-569278-2 | MP-5EU-5

**Modular Plug Kit, category 5e, 8P/8C, unshielded, 4.8 – 5.6 mm max cable jack OD, 8-position, 500/bag**

## Product Classification

Portfolio	NETCONNECT®
Product Type	Modular plug
Regional Availability	Asia   Australia/New Zealand   EMEA   Latin America   North America

## Body Features

Conductor Type	Solid   Stranded
----------------	------------------

## Configuration Features

Number of Positions	8
Keyed	No

## Contact Features

Contact Base Material	Phosphor bronze
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 µin   1.27 µm
Number of Contacts Loaded	8

## Dimensions

Cable Jacket Outside Diameter Range	0.190–0.220 in   4.8–5.6 mm
Conductor Wire Size	26–23 AWG
Insulated Conductor Outside Diameter	0.034–0.039 in   0.86–0.99 mm

## Housing Features

Housing Material	Glass filled polycarbonate
------------------	----------------------------

## Industry Standards

UL Flammability Rating	UL 1863
------------------------	---------

## Packaging Features

Packaging Quantity	500
--------------------	-----

## Product Type Features

Cable Type	Round, unshielded
Performance Category	Category 5e
Connector Style	Plug

6-569278-2 | MP-5EU-5

Jack Type	RJ45
Latch Style	Standard
Shielded	No

## Termination Features

---

Termination Method to Wire/Cable      Insulation Displacement Crimp (IDC)

## Regulatory Compliance/Certifications

---

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant