

148-90053

# HellermannTyton

Article Number: 148-90053



Description: HelaCon Plus Mini, Push-In Style Wire Connector, Double Spring, 8-Port, (PC), Black, 200/pkg

Base Data		
	Local Order Number	HCPM-8
	Type	HCPM-8
	Color	Clear (CL) Black (BK)
	Features and benefits	<ul style="list-style-type: none"> <li>• Double-spring technology for safe, secure and reliable connections.</li> <li>• Smaller footprint fits in tight spaces.</li> <li>• Low insertion force makes installation of solid or stranded copper wire fast and easy.</li> <li>• Color coded for easy identification of size.</li> <li>• Each port accepts multiple wire diameters for flexible applications.</li> <li>• Accepts 12–22 AWG solid wire and 14–22 AWG stranded wire.</li> </ul>
	Quantity Per	pack
	Brand Family	HelaCon
	Product Description	HelaCon Plus Mini Wire Connectors replace traditional twist-on wire connectors. They provide faster, easier and more reliable connection and distribution of cable and conductors in electrical installation applications. Mini connectors have a compact footprint and can be applied tool-free using convenient, push-in simplicity. Internal double-spring technology is approved for solid and stranded wires.
	GLOBAL PART NAME (auto set)	HCPM-8-PC-BK/CL
	Voltage Rating (cULus)	600 V
	Voltage Rating (VDE)	450 V
	Short Description	HelaCon Plus Mini, Push-In Style Wire Connector, Double Spring, 8-Port, (PC), Black, 200/pkg
Product Dimensions		
	Length L (Imperial)	0.65"
	Length L (Metric)	16.5mm
	Max Current	24A
	Max Voltage	600V
	Number of Conductors	8
	Width W (Imperial)	1.44"
	Width W (Metric)	36.6mm

148-90053

**HellermannTyton**

Product Dimensions	Height H (Imperial)	0.30"
	Height H (Metric)	7.70mm
	Depth D (imperial)	0.65"
	Depth D (metric)	16.5mm
Material and Specifications		
	Material	Polycarbonate (PC)
	Material Shortcut	PC
	Flammability	UL 94 V0
	Halogenfree	Yes
	Operating Temperature	-22°F to +185°F (-30°C to +85°C)
	ROHS Compliant	Yes
	UL Listed (US and Canada)	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	200
	Package Quantity (Metric)	200Pieces