



vynckier

ENCLOSURE SYSTEMS INC.



MultiboxG Series • Multi Purpose Boxes

For Electrical, Electronic and Industrial Applications

** Suffix

PC: Polycarbonate opaque cover enclosures with four stainless steel corner screws

PCCT: Polycarbonate transparent cover enclosures with four stainless steel corner screws

PCQ: Polycarbonate opaque cover enclosures with four stainless steel quick release quarter turn corner screws

PCCTQ: Polycarbonate transparent cover enclosures with four stainless steel quick release quarter turn corner screws

ABS: ABS plastic opaque cover enclosures with four stainless steel corner screws

ABSCT: ABS plastic transparent cover enclosures with four stainless steel corner screws

ABSQ: ABS plastic opaque cover enclosures with four stainless steel quick release quarter turn corner screws

ABSCTQ: ABS plastic transparent cover enclosures with four stainless steel quick release quarter turn corner screws

Features

- Enclosures are maintenance free and corrosion resistant.
- PC bases and covers are made from polycarbonate that can withstand continuous temperatures from -31°F to 176°F (-35°C to 80°C).
- PCCT bases and covers are made from polycarbonate that can withstand continuous temperatures from -31°F to 176°F (-35°C to 80°C).
- ABS bases and covers are made from polystyrene that can withstand continuous temperatures from -13°F to 104°F (-25°C to 40°C).
- ABSCT bases are made from polystyrene and covers are made from polycarbonate that can withstand continuous temperatures from -13°F to 104°F (-25°C to 40°C).
- Cover screw holes in corners are outside of the gasketed area.
- Continuous gaskets made of polyurethane foam guarantee optimal integrity.
- All enclosures can be easily modified to customer specifications.

Applications

The MultiboxG series enclosures are designed for use as electrical junction boxes or instrumentation enclosures in highly corrosive environments.

Standards

IEC 60529 (IP67)

IEC 50102 (IK08) Polycarbonate

IEC 50102 (IK07) ABS

EN 60529 (IP67)

EN 50102 (IK08) Polycarbonate

EN 50102 (IK07) ABS

Approvals

UL Listed Types 4X & 12 (Polycarbonate)

NEMA 4X & 12 (ABS)



MultiboxG Series Data Sheet

Rev 01/12/16





vynckier

ENCLOSURE SYSTEMS INC.

MultiboxG Series Data Sheet

Part Number ** Suffix (ex. MBG030302PCCTQ)	Exterior Dimensions H x W x D Inches (mm)	Interior Dimensions H x W x D Inches (mm)	Weight Lbs (kg)	Back Plate A: Aluminum S: Steel N: Non-Metallic
MBG030302PC MBG030302ABS	3.31 x 3.23 x 2.17 (84 x 82 x 55)	3.05 x 2.97 x 1.84 (77 x 75 x 47)	.15 (.07)	MBGMP33A MBGMP33S MBGMP33N
MBG030303PC MBG030303ABS	3.31 x 3.23 x 3.35 (84 x 82 x 85)	3.05 x 2.97 x 3.02 (77 x 75 x 77)	.20 (.09)	MBGMP33A MBGMP33S MBGMP33N
MBG050302PC MBG050302ABS	4.80 x 3.23 x 2.17 (122 x 82 x 55)	4.54 x 2.97 x 1.84 (115 x 75 x 47)	.26 (.12)	MBGMP53A MBGMP53S MBGMP53N
MBG050303PC MBG050303ABS	4.80 x 3.23 x 3.35 (122 x 82 x 85)	4.54 x 2.97 x 3.02 (115 x 75 x 77)	.31 (.14)	MBGMP53A MBGMP53S MBGMP53N
MBG050502PC MBG050502ABS	4.88 x 4.80 x 2.17 (124 x 122 x 55)	4.62 x 4.54 x 1.84 (117 x 115 x 47)	.43 (.20)	MBGMP55A MBGMP55S MBGMP55N
MBG050503PC MBG050503ABS	4.88 x 4.80 x 3.35 (124 x 122 x 85)	4.62 x 4.54 x 3.02 (117 x 115 x 77)	.48 (.22)	MBGMP55A MBGMP55S MBGMP55N
MBG060302PC MBG060302ABS	6.38 x 3.23 x 2.17 (162 x 82 x 55)	6.12 x 2.97 x 1.84 (155 x 75 x 47)	.31 (.14)	MBGMP63A MBGMP63S MBGMP63N
MBG060303PC MBG060303ABS	6.38 x 3.23 x 3.35 (162 x 82 x 85)	6.12 x 2.97 x 3.02 (155 x 75 x 77)	.36 (.16)	MBGMP63A MBGMP63S MBGMP63N
MBG060535PC MBG060535ABS	6.38 x 4.80 x 3.54 (162 x 122 x 90)	6.10 x 4.53 x 3.22 (155 x 115 x 82)	.51 (.23)	MBGMP65A MBGMP65S MBGMP65N
MBG080503PC MBG080503ABS	7.95 x 4.80 x 2.95 (202 x 122 x 75)	7.73 x 4.54 x 2.63 (195 x 115 x 67)	.68 (.31)	MBGMP85A MBGMP85S MBGMP85N
MBG080535PC MBG080535ABS	7.95 x 4.80 x 3.54 (202 x 122 x 90)	7.73 x 4.54 x 3.22 (195 x 115 x 82)	.73 (.33)	MBGMP85A MBGMP85S MBGMP85N
MBG080603PC MBG080603ABS	7.95 x 5.98 x 2.95 (202 x 152 x 75)	7.68 x 5.71 x 2.63 (195 x 145 x 67)	.82 (.37)	MBGMP86A MBGMP86S MBGMP86N
MBG100635PC MBG100635ABS	9.92 x 6.38 x 3.54 (252 x 162 x 90)	9.65 x 6.10 x 3.22 (245 x 155 x 82)	1.02 (.46)	MBGMP1006A MBGMP1006S MBGMP1006N
MBG100605PC MBG100605ABS	9.92 x 6.38 x 4.72 (252 x 162 x 120)	9.65 x 6.08 x 4.40 (245 x 154 x 112)	1.07 (.49)	MBGMP1006A MBGMP1006S MBGMP1006N
MBG120935PC MBG120935ABS	11.89 x 9.13 x 3.54 (302 x 232 x 90)	11.61 x 8.86 x 3.22 (295 x 225 x 82)	1.84 (.83)	MBGMP1209A MBGMP1209S MBGMP1209N
MBG120904PC MBG120904ABS	11.89 x 9.13 x 4.33 (302 x 232 x 110)	11.61 x 8.86 x 4.00 (295 x 225 x 102)	1.89 (.86)	MBGMP1209A MBGMP1209S MBGMP1209N

Rev 01/12/16

