

EDL-416EN/WS - PA Loudspeaker



Moisture-proof PA ball speaker, with EN 54-24 certification, 1438-CPR-0535.

- 100 V line technique
- White ABS housing (UL 94HB), UV-resistant and weatherproof
- Moisture-proof speaker cone
- Supplied with 450 cm connection cable and canopy
- Ceramic connection terminal, thermal fuse

Technical Data

Active/passive	: passive
Line technique	: 100 V
Impedance	: -
Frequency range	: 130-18,000 Hz
Amplifier power	: -
Max. power	: -
THD	: -
S/N ratio	: -
Input signal	: -
System	: 130 mm full range speaker
Full range speaker	: -
Bass speaker	: -
Midrange speaker	: -
Tweeter	: -
Number of speakers	: 1
Speaker size	: 13 cm (5")
Power rating	: 16/8/4 W
Peak music power output	: -
Sensitivity	: 89.9 dB/W/m
Max. rated SPL	: 101 dB
Radiation angle, horizontal	: 196° (1 kHz) 132° (2 kHz) 170° (4 kHz)
Radiation angle, vertical	: 196° (1 kHz) 132° (2 kHz) 170° (4 kHz)
Features	:
Material (housing/cabinet)	: ABS
Colour	: white, RAL9010
Mounting facility	: canopy
Protected against ball rebound	: -
Protective class	: IP35
Admiss. ambient temp.	: -20 °C to +80 °C
Power supply	: -
Width	: Ø 185 mm
Height	: 157 mm
Depth	: -
Weight	: 1.5 kg
Inputs	: ceramic terminal with thermal fuse



CPC
FULWOOD
PR29PP
03447 880088

Outputs	: -
Replacement voice coil	:
Other features	: -