


ALS30, Aluminum Electrolytic, 85C, 470 uF, 20%, 250 V, -40/+85C

**Dimensions**

D	36mm +/-1mm
L	52mm +/-2mm
T	7.14mm +/-0.5mm
S	12.8mm +/-0.5mm
DT	8mm +/-0.5mm
LT	58.5mm +/-1mm
TD	10mm MIN
V	8mm NOM

Packaging Specifications

Weight:	75 g
Sleeving:	Yes
Packaging:	Bulk, Box

General Information

Supplier:	KEMET
Series:	ALS30
Dielectric:	Aluminum Electrolytic
Description:	Screw Terminal, Aluminum Electrolytic
RoHS:	Yes
Notes:	Dimensions D And L Include Sleeving. MS (MxH) = M8x12

Specifications

Capacitance:	470 uF
Capacitance Tolerance:	20%
Voltage DC:	250 VDC
Temperature Range:	-40/+85C
Rated Temperature:	85C
Life:	11000 Hrs (Rated Voltage And Ripple Current At 85C), 22000 Hrs (Rated Voltage At 85C)
Resistance:	247 mOhms (100Hz 20C), 187 mOhms (10kHz 20C)
Current:	3 Amps (100Hz 85C), 4.5 Amps (10kHz 85C)
Leakage Current:	705 uA (5min 20C)