Product data sheet Characteristics

METSECT5CC013

current transformer tropicalised DIN mount 125 5 for cables d. 21





Main

		specific user applications
Main		specific
Range	PowerLogic	
Product name	СТ	products
Product or component type	Current transformer	O D
Secondary current	5 A	of thes
Accuracy class	Class 3 maximum power: 4 VA Class 0.5 maximum power: 2.5 VA Class 1 maximum power: 3.5 VA	or reliability o
[In] rated current	125 A	
Complementary		mining suitability

Complementary

Current transformer type	Tropicalised for cable
Current transformer ratio	125/5
[Ith] conventional free air thermal current	7.5 kA
Dynamic withstand current	2.5 lth
Safety factor	<= 5
[Ue] rated operational voltage	< 720 V AC at 50/60 Hz
[Ui] rated insulation voltage	3 kV
Mounting mode	By screws Clip-on
Mounting support	Mounting plate DIN rail
Width	44 mm outside
Height	65 mm outside
Depth	30 mm outside
Diameter	21 mm
Product weight	0.175 kg
[Uimp] rated impulse withstand voltage	3 kV
Electrical insulation class	Class B

Cable outer diameter	21 mm max
Sealing	With

Environment

Standards	IEC 61869-2 VDE 0414
Product certifications	EAC CE
IP degree of protection	IP20
Relative humidity	095 %
Ambient air temperature for operation	-2560 °C

Offer Sustainability

Green Premium product	
Compliant - since 1427 - Schneider Electric declaration of conformity	
Schneider Electric declaration of conformity	
Reference not containing SVHC above the threshold	
Reference not containing SVHC above the threshold	
Available	
Need no specific recycling operations	
	Compliant - since 1427 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold Available