



WRAPTOR Series Nylon Cloth Labels

Part Number: WRAP-9-499

Label/Tape Size: 2 in H x 2 in W

Material: Nylon

Material Number: B-499

Color: White



OVERVIEW

Nylon Cloth (B-499) wrap-around labels are highly pliable to conform to tightly curved surfaces such as wire and cable.

- Matte white polyamide coated nylon cloth material has a permanent acrylic adhesive and is thermal transfer printable
- Recommended for indoor use
- RoHS compliant to 2005/618/EC MCV amendment to RoHS Directive 2002/95/EC; UL approved; CSA accepted
- Service temperature of -40 to 193° F (-40 to 90° C)
- **SPECIFICATIONS**

Anti-Skid Surface?	N/A
Material Number	B-499
Dimensions	2 in H x 2 in W
UOM	Roll of 2100 Labels
Finish	Matte
Indoor or Outdoor Use	N/A
Label/Tape Size	2 in H x 2 in W
Maximum Service Temperature °F	194 °F
Maximum Wire Diameter	0.64 in
Maximum Wire Gauge	3/0 gauge
Minimum Service Temperature °F	-40 °F
Minimum Wire Diameter	0.25 in
Minimum Wire Gauge	8 gauge
Pre-Printed Areas on Label	Colored Write-On Area
Printable Area Dimensions	2 in H x 2 in W
Printable Area Height	2 in
Printable Area Width	2 in
Product Number	60628
UPC	662820606284
Quantity per Roll	2100
Quantity per Row	1
Tamper Indication Type	N/A
Thickness	0.0065 in
Trade Name	Wraptor™
Adhesive Type	Acrylic
Applications	Cable & Wire Marking, Panel Labeling
Color	White
For Use with Printer	WRAPTOR™ Wire Marking System

Header	No Header
Label/Media Format	Roll
Material	Nylon
Material Properties	Autoclavable, Cryogenic storage
Print Technology	Thermal Transfer
Resistance Properties	Abrasion-Resistant, Chemical-Resistant, Humidity-Resistant, UV-Resistant, Weather-Resistant
Shape	Square
Suggested Ribbon Series	R4300