



6W

VT-1965 6W LED CANDLE BULB COLORCODE:3000K B22

Equivalent
40W

Lumens
470

Beam Angle
200

Dimensions
37x102mm

Warm White
SKU:4440



2 YEARS
WARRANTY



Technical Information

Instant Start: 0-100% in 11s

EQ-WATTS: 40

Watts: 6

Lumens: 470

Holder Type: B22

Shape: CANDLE

Beam Angle: 200

Body Type: Thermoplastic

Energy Rating: A+

Long life: 20,000 Hours

LED Chip Type: SMD

IP Rating: IP20

Dimmable: No


Warranty (Years): 2

PF: >0.5

CRI: >80

Operation Temperature: -25 to +50°C

Input Power: AC:220-240V,50Hz



Features

- ✓ Stable SMD technology which makes the product more reliable and durable
- ✓ Uses 80% less energy and lasts 20 times longer than Standard Bulbs
- ✓ LED Bulbs are the best replacement for conventional Incandescent or Fluorescent Bulbs
- ✓ High endurance and Durability
- ✓ Excellent Heat Radiation Efficiency
- ✓ Aluminium & Thermoplastic Body options available
- ✓ High luminous efficacy & Low Power consumption
- ✓ Excellent Power factor & Integrated IC driver
- ✓ No Flickering - No UV Radiation - No Mercury
- ✓ Broad Range of holders like E27, E14, B22, B15 .
- ✓ Application - Residential Lighting, Commercial Lighting, Decorative, Living Room, Lounge etc



Note: Suitable & Recommended for maximum daily use of 10-12 hours

Packaging

Unit Details

Length(Box)mm	38
Width(Box)mm	38
Height(Box)mm	100
Unit CBM	0.000143

Listing Details

EAN Code	3800157607667
Commodity Code	9405403990

Master Box Packaging

Master Box Qty (Pcs Per Carton)	200
---------------------------------	-----

READY STOCKS IN
UK & EU



Dispatch within
24 Hours

www.vtacexports.com

OUR PRODUCTS ARE
CURRENTLY SOLD IN OVER
70
COUNTRIES