

ROCKER SWITCHES

PRODUCT NUMBER 3251.0048



TECHNICAL DATA

Product number	3251.0048
Business unit	Switches, Sensors & Controls
Product family	Rocker switches
Actuation type	direct
Miscellaneous	with pre assembled cap / circuit symbol: 50.43
Weight	24.500 g
ROHS conform	yes
Product code	3250-1A-00-1-0 A0-bl-1540-0000-00
Switching function	ON / OFF switch (SPST)
Material fixed contact	AgNi
Number of poles	1 - pole
connections	Quick-connect terminal, 3.0 x 0.8
Mechanical life endurance	50E4
Rating IEC	10 (5) A 12 - 24 V DC 1E5
Contact resistance (new condition)	< 100 (1 A 12 V DC) mOhm
Insulation resistance (new condition)	> 100 (500 V DC) MOhm
Proof tracking	250 PTI
Protection type	→ Connection IP 40 → Actuator IP 66 and IP 67
Ambient temperature	-40 °C ... +85 °C
Ambient temperature	-40 °C ... +85 °C
Actuators and additional actuators	rocker: PC, transparent white, black varnished, lasered symbol
Housing description	housing: PP, black base plate: PA, black
Connection surface	→ bearing connection silver plated → external connection silver plated
Contact material	AgNi
Operating force	7 N to 12 N +1,5 N
Miscellaneous	Circuit symbole 50.43
Additional labeling	50.43
Type of fastening	Snap fastening

Technical changes reserved. Dimensions are not binding.
Detailed specifications available on request.

Marquardt GmbH · Schloss-Straße 16 · 78604 Rietheim-Weilheim · Germany
Phone: +49 (0) 7424 / 99-0 · Fax: +49 (0) 7424 / 99-2399 · www.marquardt.com · marquardt@marquardt.de