

PNOZ m EF 4DI4DOR

772143



Configurable control system PNOZmulti 2 expansion module 4 safe digital inputs, 4 safe relay outputs.

Technical details

Approvals:	CE;cULus Listed;TÜV;BG;CCC
Number of digital inputs:	4
Number of relay outputs:	4
Terminal style:	Plug-in
Version for extreme environ. conditions:	Standard
Width dimension:	22.5 mm
Height dimension:	101.4 mm
Depth dimension:	120.0 mm
Gross weight:	205 g
Net weight:	190 g
Ambient temperature:	0 - 60 °C

Accessories



750004

PNOZ s Setscrew terminals 22,5mm



751004

PNOZ s Setspring loaded terminals 22,5mm

Optional accessories



779260

PNOZ mm0.xp connector left (10 pcs)
