

# HL 2020 E – The professional hot air tool for DIYers

**New - available**

- **20% higher durability!**
- **Optimised protection for you: an optical indication will warn against the danger of burnings at the outlet tube; as well after separation of network!**
- **The novel joystick creates a completely new and intuitive operation**

## Technical Data

Dimensions (LxBxH):	253 x 85,5 x 200 mm
Voltage:	220-230 V, 50/60 Hz
Output:	2200 W
Temperature:	80 - 630 °C, continuously adjustable in 10°C steps
Airflow	150 / 300 / 500 l/min
Stages:	3 (Airflow)
Specials:	Optical warning against burnings, new intuitive operation, power cord exchange- able, optimised centre of gravity, display, hanger, optional new accessory: HL Scan and fine dust particle filter
Length power cord:	2,20 m
Motor:	brush motor
Heating element:	Ceramic heating element



# HL 2020 E – The professional hot air tool for DIYers

New - available

- Weight of packaging:                      gross: 1848 g              net: 860 g
- Dimensions of packaging:                395 x 100 x 320
- Customs tariff number:                    84198998 UL RO
- Country of origin:                          Romania
- Region of origin:                            03
- Weight of paper/papboard packaging: 0 g
- Weight of plastic packaging:            1000 g



No print-version! Feel free to ask for a printable product image.