

Share:



SURTA48XLBP

★★★★★
Be the first to [write a review](#)
Share this Product:



Includes : Documentation CD , User Manual

- Product Overview
- Technical Specifications**
- Documentation
- Options
- Ratings & Reviews

Input		Print Technical Specification
Number of Power Cords	1	
Batteries & Runtime		
Battery type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof	
Included Battery Modules	2	
Battery mounting	Enclosed battery cabinet	
Expected Battery Life (years)	3 - 5	
RBC Quantity	2	
Battery blocks per string	4	
Physical		
Maximum Height	17.8inches (452mm , 45.2CM)	
Maximum Width	3.4inches (86mm , 8.6CM)	
Maximum Depth	22.0inches (559mm , 55.9CM)	
Rack Height	2U	
Net Weight	72.4lbs. (32.91KG)	
Shipping weight	81.6lbs. (37.09KG)	
Shipping Height	10.0inches (254mm , 25.4CM)	
Shipping Width	24.0inches (610mm , 61.0CM)	
Shipping Depth	28.75inches (730mm , 73.0CM)	
Color	Black	
Units per Pallet	12.0	
Environmental		
Operating Temperature	32 - 104 °F (0 - 40 °C)	
Operating Relative Humidity	0 - 95% no %	
Operating Elevation	0-10000ft (0-3000meters)	
Storage Temperature	-20 - 50 °C	
Storage Relative Humidity	0 - 95% no %	
Storage Elevation	0-50000ft (0-15000meters)	
Conformance		
Standard warranty	2 years repair or replace	
Sustainable Offer Status		
RoHS	Compliant	
EOL	Available in Documentation tab	

Email

I am a...

[Contact Us](#)
[Rate this website](#)

[TERMS & CONDITIONS](#) | [PRIVACY STATEMENT](#)

© 2018, APC by Schneider Electric

