

Product information

10.8V Jigsaw BL CXT



JV103DZ

Capacity in Aluminium	20 mm
Battery Type	Li-ion
Body only machine	1
Voltage	10.8 v
Capacity in Mild Steel	10 mm
Capacity in Wood	90 mm
Settings	3 orbital + straight cut
Stroke Length	23 mm
Noise sound pressure	85 dB(A)
Noise sound power	96 dB(A)
Noise K factor	3 dB(A)
No Load Speed	800 - 3000 spm
Vibration K factor	1.5 m/sec ²
Vibration: Cutting Chipboard	8.5 m/sec ²
Vibration: Cutting Sheet Metal	6.0 m/sec ²
Net weight	2.0 kg



STANDARD EQUIPMENT: Jigsaw blade, Hex wrench

- Brushless motor
- Ergonomic top handle design
- Electric brake
- Variable speed
- Soft start
- "Soft no load" function automatically reduces the motor speed during idling to suppress the vibration of the machine body.
- Constant speed control
- LED job light
- Tool-less blade change.
- Change lever for 3 orbital settings and straight cutting.
- Bevel capacity 0 - 45 degrees Left / Right
- Lock on function

Details correct as of: 9-1-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

www.makitauk.com