

SDSQUAR-016G-GN6MA

16GB SANDISK ULTRA microSDHC CLASS 10 MEMORY CARD



SPECIFICATIONS	
Capacity	16 GB
Read Speed	Up to 98MB/s
Form Factor	microSDHC
Video Speed	C10, A1
SD Adapter	Yes
Performance	Up to 100MB/s read speed
Dimension	0.59in x .043in x .03in (14.99mm x 10.92mm x 1.02mm)
Operating temperature	-13ºF to 185ºF (-25ºC to 85ºC)
Storage temperature	-40°F to 185°F (-40°C to 85°C)
Compatibility	Compatible with microSDHC and microSDXC supporting host devices