

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0151341001

Status:

Active

Overview:

PicoBlade Connector System

Description:

PicoBlade-to-PicoBlade Off-the-Shelf (OTS) Cable Assembly, Single Row, 100.00mm Length, 10 Circuits, Natural



Series image - Reference only

Documents:

[Drawing \(PDF\)](#)

[Product Literature \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General	
Product Family	Cable Assemblies
Series	15134
Assembly Configuration	Dual Ended Connectors
Connector to Connector	PicoBlade-to-PicoBlade
Overview	PicoBlade Connector System
Product Literature Order No	987651-6143
Product Name	PicoBlade OTS
UPC	191128411806
Physical	
Cable Length	100.00mm
Circuits (Loaded)	10
Color - Resin	Natural
Gender	Female-Female
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	4.550/g
Packaging Type	Bag
Pitch - Mating Interface	1.25mm
Plating min - Mating	0.889µm
Plating min - Termination	0.914µm
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	0.90mm
Wire Size AWG	28
Wire/Cable Type	UL 1061
Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	125V

Material Info

Reference - Drawing Numbers

Sales Drawing

2012343240-000

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/30/2017 (7 July
2017)

Halogen-Free

Status

Not Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

15134 Series

Mates With

PicoBlade Header [53261](#) , [53047](#) , [53398](#) ,
[53048](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION