

Coaxial Cable Connector 11_SMA-50-2-5/111_N

Description

Straight cable plug

Interface standards

IEC 60169-15_MIL-STD-348A/310_CECC 22110



Technical Data

Electrical Data

| | |
|--------------------------|-------------|
| Impedance | 50 Ω |
| Interface frequency max. | 18 GHz |

Mechanical Data

| | |
|----------------|-----------|
| Centre contact | soldered |
| Outer contact | crimped |
| Weight | 0.0037 kg |

Environmental Data

| | |
|-----------------------|------------------|
| Operating temperature | -65 °C to 165 °C |
| 2011/65/EU, RoHS | compliant |

Material Data

| Piece Parts | Material | Surface Plating |
|----------------|------------------------|--|
| Centre contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Outer contact | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Body | Copper Beryllium Alloy | Gold Plating (Nickel underplated) |
| Insulator | PFA / PTFE | |
| Coupling nut | Bronze | Gold Plating (Nickel underplated) |
| Gasket | VMQ (Silicone rubber) | |
| Crimp ferrule | Copper | Gold Plating (without Nickel underplating) |

Related Documents

| | |
|----------------------|----------------|
| Outline drawing | DOU-00006531 |
| Catalogue drawing | DOU-00006102 |
| Assembly instruction | DOC-0000179309 |

Ordering Information

| | |
|----------------------|----------------------|
| Bulk 100 pcs package | 11_SMA-50-2-5/111_NH |
| Single package | 11_SMA-50-2-5/111_NE |

Additional Information

| | |
|-----------------|---|
| Suitable cables | RG_316_U, ENVIROFLEX_316, RG_188_AU, RG_174_U |
|-----------------|---|