

## Plastic Garden Lamp Model: PEL00828

**Please read these instructions carefully before use and retain for future reference.**

### **IMPORTANT SAFETY INFORMATION**


- When using electrical appliances basic safety precautions should always be followed.
- Check that the voltage indicated on the rating plate corresponds with that of the local network before connecting the appliance to the mains power supply.

### **Safety Information for Installation and Operation**

- Avoid excessive force when installing.
- Always install on a surface that can support the weight of the fixture.

## INSTALLATION

- Turn off or isolate the mains supply.
- Feed the supply wiring through the access point in the main body.
- Mount the main body onto the wall or ceiling using a suitable mounting method.
- Connect the positive supply wire (brown or red) to the lamp holder terminal marked L.
- Connect the neutral supply wire (blue or black) to the lamp holder terminal marked N.
- Fit an appropriate lamp E27 Max 11W (not supplied).
- Place the diffuser onto the main body aligning the screw position cut outs.
- Attach the diffuser cover onto the main body by lining up the three screw positions then fit and tighten the screws.
- Restore the mains supply.



## CLEANING AND MAINTENANCE

- Clean only with a soft, dry cloth. Do not use any chemicals, abrasives or solvents that may damage the product.

## SPECIFICATIONS

Voltage	220-240V~50Hz <input type="checkbox"/>
IP rating	IP44
Lamp type	E27 11W Fluorescent or LED



### INFORMATION ON WASTE DISPOSAL FOR CONSUMERS OF ELECTRICAL & ELECTRONIC EQUIPMENT.

When this product has reached the end of its life it must be treated as Waste Electrical & Electronic Equipment (WEEE). Any WEEE marked products must not be mixed with general household waste, but kept separate for the treatment, recovery and recycling of the materials used. Contact your local authority for details of recycling schemes in your area.



Made in China. PR2 9PP

Man Rev 1.0