Product data sheet

Miniature





Product description Contacts: 16, female panel mount connector, solder, 12 - 19 contacts, gold plated contacts

Area M16 IP40 Series 581/680/682

Order number **09 0340 00 16**







You can find the assembly instructions on the next page.

-40 °C

Technical data

General values

Connector design Connector locking system Termination Wire gauge (mm) Wire gauge (AWG) Upper limit temperature Lower limit temperature female panel mount connector bolted solder 0,25 mm² 24 85 °C

Electrical values

Rated voltage 60 V Rated impulse voltage 500 V Pollution degree Overvoltage category Insulating material group Ш Rated current (40 °C) 3 A Volume resistivity $\leq 3 \text{ m}\Omega$ EMC compliance Shielding is not possible IP40 Degree of protection > 500 Mating cycles Mechanical operation

Material

Contact material CuSn (bronze)
Contact plating Au (gold)
Contact body material PBT (UL 94 V-0)

Product data sheet


Miniature



Product description Contacts: 16, female panel mount connector, solder, 12 - 19 contacts, gold plated contacts

Area M16 IP40 Series 581/680/682

Order number **09 0340 00 16**



Product data sheet

Miniature



Product description Contacts: 16, female panel mount connector, solder, 12 - 19 contacts, gold plated contacts

Area M16 IP40 Series 581/680/682

Order number **09 0340 00 16**

Sicherheitshinweise

The connectors are designed for use in plant, control system and electrical equipment. The end user is responsible for checking whether the connectors are suitable for use in other applications.