


PART		MATERIAL
HANDLE	1	ABS
BODY	1	BSBM
5.5mm INSULATOR	1	EBONITE
LUG	2	BST
INSULATOR	1	EBONITE
CONTACT CENTER PIN	1	BSBM



OPERATING TEMPERATURE : -25~+70°C HUMIDITY : Max 85%
 NOMINAL RATINGS : VOLTAGE : 3.15~13.5VDC CURRENT : 2A
 INSULATION RESISTANCE : Min 50MΩ at 500V (First Current Flow)
 VOLTAGE BREAKDOWN : 1 Minute at Max 500VAC
 CONTACT RESISTANCE : Max 30mΩ at 10mV/1A (First Current Flow)

(Subject to EIAJ RC-5320 Standards)

1999.8.25 Tolerance +/-0.03 is changed to +/-0.05.
 Other tolerance : 0.3

DATE: 1-05-2017

UNIT	SCALE	
MM	2:1	2.5 x 5.5 x 14
ITEM#		27-5904

PHC