

MA130 Mini 200A AC Clamp Meter



Easy-to-use pocket-sized mini clamp meter allows measurements in tight locations. Jaw opening fits conductors up to 300MCM. Manual ranging Current measurements with three ranges to choose from. Features data hold to freeze reading on display and Max hold to record maximum Current reading. Bright backlit display allows user to easily view in dimly lit areas.



Features

- Mini pocket-sized design with backlit LCD display and 0.6" (16mm) jaw size fits conductors up to 300MCM
- CAT III - 300V, CAT II-600V ratings
- Data Hold freezes reading on display
- Max Hold displays maximum reading
- Large LCD with backlit feature for viewing in dimly lit area
- Auto Power Off
- Complete with two AAA batteries

Specifications	Range	Max Resolution	Basic Accuracy
AC Current	2.000A	1mA	±(4% + 30d)
	20.00A	10mA	
	200.0A	100mA	
Dimensions	6.2x2.4x1.3" (158x60x33.5mm)		
Weight	6oz (170g)		

Ordering

MA130 Mini 200A AC Clamp Meter



UPC Code: 793950371305