



Figure similar

LOGO! 24CEO, logic module, without display, PS/I/O: 24 V/24 V/24 V trans., 8 DI (4AI)/4DO, memory 400 blocks, modular expandable, Ethernet, integr. web server, data log, user-defined Web pages, standard microSD card for LOGO! Soft Comfort V8 or higher, older projects executable

Installation type/mounting	
Mounting	on 35 mm DIN rail, 4 spacing units wide
Supply voltage	
Rated value (DC)	
• 24 V DC	Yes
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Time of day	
Time switching clocks	
• Number	400; Max. 400, function-specific
• Power reserve	480 h
Digital inputs	
Number of digital inputs	8; Of which 4 can be used in analog mode (0 to 10 V)
Digital outputs	
Number of digital outputs	4; Transistor
Short-circuit protection	Yes; electrical (1 A)

Output current	
for signal "1" permissible range for 0 to 55 °C, max.	0.3 A
EMC	
Emission of radio interference acc. to EN 55 011	
Limit class B, for use in residential areas	Yes; Radio interference suppression according to EN55011, Limit Value Class B
Degree and class of protection	
Degree of protection acc. to EN 60529	
IP20	Yes
Standards, approvals, certificates	
CE mark	Yes
CSA approval	Yes
UL approval	Yes
FM approval	Yes
developed in accordance with IEC 61131	Yes
according to VDE 0631	Yes
Marine approval	Yes
Ambient conditions	
Ambient temperature during operation	
min.	-20 °C; No condensation
max.	55 °C
Ambient temperature during storage/transportation	
min.	-40 °C
max.	70 °C
Altitude during operation relating to sea level	
Ambient air temperature-barometric pressure-altitude	Tmin ... Tmax at 1 080 hPa ... 795 hPa (-1 000 m ... +2 000 m)
Dimensions	
Width	71.5 mm
Height	90 mm
Depth	58 mm
last modified:	02/09/2018