

Model#: 29-9505**Product Specifications**

Built-in Battery	20000mAh,3.7V,74Wh High Rate Discharge Lithium Polymer Batteries
Input charging	DC15V/1A
Fully Charged Time	DC 15V/1A:6~7 hours
Charge mode	CC/CV
Jumpstart Output	EC5; Support 12V Battery System Vehicle
Output	DC(12V~16V)/15A Max Dual USB outputs, 5V/3.1A Max
DC Wattage(MAX)	180W
Bulb Type	Ultra bright LED light/SOS
Power Indicator	4 Indicators
Peak Current	1000A
Operation temperature	-10°C-60°C
Lifecycle	500 times
MultiSafety Protection 2.0	a.Delay protection b.Short-circuit protection c.Reverse polarity protection d.Over-current protection e.Over-voltage protection f.Low-voltage protection g.Reverse filling protection h.Overfrequency protection i.Over-temperature protection

Package includes

- 1 x Tool bag
- 1 x car jump starter
- 1 x Smart clamps T104
- 1 x power adapter
- 1 x microUSB charging cable
- 1 x car charger
- 1 x cigarette light adapter
- 1 x user manual

Benefits**Peak Current up to 1000A**

- 1.Built in 20000mAh /3.7V High Rate Discharge Lithium Polymer Batteries
- 2.Peak Current is up to1000A
- 3.Jumpstart 12V Diesel up to 8.0L|Gasoline:Fully support
- 4.Support up to 180W DC power For Car Kits
- 5.USB 5V/3.1A for mobile phones
- 6.Ultra bright torch/blink/SOS
- 7.Weight 780g, Light Weight to carry
- 8.Equipped with SmartClamps T104.
- 9.Mistake proof including: Shortcircuit, Reverse polarities proof etc.,