

IMPORTANT LINKS

- FEATURES & SPECS
- WARRANTY
- FAQS
- USER REVIEWS

FEATURES & SPECS

FEATURES

- DEWALT® 20V Max* XR Premium Lithium Ion batteries offer longer tool run-time and enhanced durability
- 3-speed, all-metal transmission matches the tool to task for fastest application speed and improved run time
- Heavy-duty 1/2" metal ratcheting chuck with carbide inserts provides superior bit gripping strength
- LED light with 20-second delay after trigger release
- High power, high efficiency motor delivers 535 unit watts out of max power for superior performance in all drilling and fastening applications

SPECIFICATIONS

| | |
|---------------------|------------------|
| CHUCK SIZE | 1/2" |
| CHUCK TYPE | METAL RATCHETING |
| CLUTCH SETTINGS | 22 |
| MAX POWER | 535 UWO |
| # OF SPEED SETTINGS | 3 |
| POWER TOOL TYPE | CORDLESS |
| SYSTEM | 20V MAX* |

INCLUDES

- 1 hour charger
 - 360° side handle
- (2) 20V Max* XR Premium Lithium Ion batteries
 - Kit Box

WARRANTY & SERVICE INFORMATION

WARRANTY INFORMATION