

FEATURES & SPECS

FEATURES

- DEWALT built brushless motor and XR Lith-Ion batteries deliver more run time and capacity over standard units
- 3-speed settings for optimized application versatility
- Precision drive in speed 1 for precision applications and added control
- 3 LEDs with 20-second delay after trigger release, provide visibility without shadows
- One-handed loading 1/4" hex chuck with easy grip sleeve, accepts 1" bit tips
- Compact and lightweight design to fit into tight areas (6 mm shorter than the previous DCF886)

SPECIFICATIONS

BATTERY TYPE	LITHIUM ION
IMPACTS/MIN	0-3,800 IPM
NO LOAD SPEED	0-1,000/ 2,800/ 3,250
POWER TOOL TYPE	CORDLESS
SYSTEM	20V MAX*
TOOL LENGTH	5.3 IN
TOOL WEIGHT	2.0 LBS
VARIABLE-SPEED TRIGGER	YES

INCLUDES

- DCF887 - 20V MAX* XR 1/4" 3-Speed Impact Driver
- Belt Hook

WARRANTY & SERVICE INFORMATION

WARRANTY INFORMATION