

## Diagonal HD Cutting Pliers Angled Head



## Product Features

Angled head design for easy work in confined spaces  
Cuts ACSR, screws, nails and most hardened wire  
High-leverage design. Rivet is closer to the cutting edge for 36% greater cutting and gripping power than other plier designs  
Short jaws and beveled cutting edges permit close cutting of wire  
Induction-hardened cutting knives for long life  
Hot-riveted joint ensures smooth action and no handle wobble  
State-of-the-art, dual-material Journeyman™ handles provide a better grip without sacrificing tool strength and durability  
Hard, black material for toughness and durability  
Soft material on outer surface for comfort and a firm grip  
Color-coded handles allow quick identification of tool  
Custom, US-made tool steel



**BUY NOW**

**FIND RETAILER**

## Specs

## Video

## Downloads

## Warnings

## Accessories

**Type:** Heavy Duty High Leverage Diagonal Cutting Pliers

**Material:** Steel

**Jaw Length:** 13/16" (20.6 mm)

**Jaw Thickness:** 13/16" (20.6 mm)

**Cutting Knives:** Standard

**Joint Type:** Hot Riveted

**Handle Finish:** Journeyman

**Insulated:** No

**Weight:** 0.61 lb (0.28 kg)

**Application:** ACSR, Screws, Nails, Most Hardened Wire

**Overall Length:** 8-1/8" (206.4 mm)

**Nose Type:** Angled

**Jaw Width:** 1-3/16" (30.2 mm)

**Jaw Capacity:** 3/4" (19.1 mm)

**Cut Style:** Standard

**Handle Color:** Light Blue/Black

**Handle Length:** 6-3/4" (171.5 mm)

**Tether Capable:** No

**UPC:** 092644721106

[partner support](#) | [american manufacturing](#) | [klein tradesman club](#) | [warranty](#) | [contact us](#) | [klein gear](#)