

CAMDENBOSS CAMCIRC RANGE IP68 MULTIPOLE CONNECTORS



- Brass bodied 'push-pull' connectors
- IP 68 rated
- 4 body sizes
- Available from 2 to 19 poles
- A range of styles and configurations available
- Keycode 1 supplied as standard



Type A	Plug	
Type B	Fixed Socket	
Type D	Fixed Socket	
Type E	Fixed Socket	
Type L	Fixed Socket	
Type M	Fixed Socket	
Type S	Cable Mount Socket	
Type T	Cable Mount Socket	

102 Size	
103 Size	
1031 Size	
104 Size	

Part Number Selection Table							
Series	Body	Size	Style	Key	Shielding	Poles	
CC	X	X	X	1	/	X	XX
A - Plug B - Fixed Socket Flat D - Fixed Socket Protruding E - Fixed Socket Protruding L - Fixed Socket Edged M - Fixed Socket Through Panel S - Cable Mount Socket T - Cable Mount Socket U - Cable Clamp Set E3 V - Cable Clamp Set E31 W - Cable Clamp Set E32 1 - 102 Size 2 - 103 Size 3 - 1031 Size 4 - 104 Size P - Plug S - Socket C - Clamp Set 1 - Key Code / A - Shielded B - Unshielded C - Environmental 3-19 - Poles/Pins							

Part Number Examples							
CC	A	1	P	1	/	A	03
Plug 102 Size, Shielded, 3 pin							
Part Number Examples							
CC	M	1	S	1	/		05
Fixed Receptacle 102 Size, Type M, 5 pin							
Part Number Examples							
CC	V	2	C		/	A	J
Cable clamp Set 103 size, Shielded, 5.7 to 6.2 wire size							

CAMDENBOSS

CAMCIRC RANGE

IP68 MULTIPOLE CONNECTORS



		Mating Halves - Plugs to Receptacles															
		Plugs															
		CCA1P1/A03	CCA1P1/A04	CCA1P1/A05	CCA1P1/A07	CCA1P1/A09	CCA2P1/A03	CCA2P1/A04	CCA2P1/A05	CCA2P1/A06	CCA2P1/A07	CCA2P1/A08	CCA3P1/A10	CCA3P1/A12	CCA3P1/A19	CCA4P1/A16	CCA4P1/A19
Fixed Mount Receptacles	CCB1S1/03	•															
	CCB1S1/04		•														
	CCB2S1/03						•										
	CCB2S1/04							•									
	CCB2S1/06								•								
	CCB2S1/07									•							
	CCB2S1/08											•					
	CCB3S1/19														•		
	CCB4S1/19																•
	CCD2S1/04							•									
	CCE1S1/03	•															
	CCE1S1/05			•													
	CCE1S1/07				•												
	CCE2S1/07										•						
	CCL2S1/06									•							
	CCM1S1/03	•															
	CCM1S1/05			•													
	CCM1S1/07				•												
	CCM1S1/09					•											
	CCM2S1/05								•								
CCM2S1/07										•							
CCM3S1/10												•					
CCM3S1/12													•				
CCM4S1/16															•		
Cable Mount Receptacles	CCS1S1/04		•														
	CCT1S1/03	•															
	CCT1S1/05			•													
	CCT1S1/07				•												
	CCT2S1/05							•									
	CCT2S1/07										•						

		Clamp Pairing			
		Plugs			
		CCA1P1	CCA2P1	CCA3P1	CCA4P1
Cable Clamp Sets	CCU1C	•			
	CCU3C			•	
	CCU4C				•
	CCV1C	•			
	CCV2C		•		
	CCW1C	•			

CAMDENBOSS CAMCIRC RANGE IP68 MULTIPOLE CONNECTORS



Table of Suggested Alternatives				
	CamCirc Part	Fischer Part		
Cable Mounting Plugs	CCA1P1/A03	S 102 A052-130+	Cable Mounting Plugs	
	CCA1P1/A04	S 102 A053-130+		
	CCA1P1/A05	S 102 A054-130+		
	CCA1P1/A07	S 102 A056-130+		
	CCA1P1/A09	S 102 A059-130+		
	CCA2P1/A03	S 103 A052-130+		
	CCA2P1/A04	S 103 A053-130+		
	CCA2P1/A05	S 103 A054-130+		
	CCA2P1/A06	S 103 A056-130+		
	CCA2P1/A07	S 103 A057-130+		
	CCA2P1/A08	S 103 A058-130+		
	CCA3P1/A10	S 1031 A010-130+		
	CCA3P1/A12	S 1031 A012-130+		
	CCA3P1/A19	S 1031 A019-130+		
CCA4P1/A16	S 104 A086-130+	Fixed Receptacle Sockets		
CCA4P1/A19	S 104 A092-130+			
Fixed Receptacle Sockets	CCB1S1/03		D 102 A052-130	
	CCB1S1/04		D 102 A053-130	
	CCB2S1/03		D 103 A052-130	
	CCB2S1/04		D 103 A053-130	
	CCB2S1/06		D 103 A056-130	
	CCB2S1/07		D 103 A057-130	
	CCB2S1/08		D 103 A058-130	
	CCB3S1/19		D 1031 A019-130	
	CCB4S1/19		D 104 A092-130	
	CCD2S1/04		DBEE 103 A053-130	
	CCE1S1/03		DBEU 102 A052-130	
	CCE1S1/05		DBEU 102 A054-130	
	CCE1S1/07		DBEU 102 A056-130	
	CCE2S1/07		DBEU 103 A057-130	
	CCL2S1/06		DEE 103 A056-130	
	CCM1S1/03		DEU 102 A052-130	
	CCM1S1/05		DEU 102 A054-130	
	CCM1S1/07		DEU 102 A056-130	
	CCM1S1/09		DEU 102 A059-130E	
	CCM2S1/05		DEU 103 A054-130	
CCM2S1/07	DEU 103 A057-130			
CCM3S1/10	DEU 1031 A010-130			
CCM3S1/12	DEU 1031 A012-130			
CCM4S1/16	DEU 104 A086-130			
Cable Mounting Sockets	CCS1S1/04		K 102 A053-130+	Cable Mounting Sockets
	CCT1S1/03		KE 102 052-130+	
	CCT1S1/05	KE 102 A054-130+		
	CCT1S1/07	KE 102 A056-130+		
	CCT2S1/05	KE 103 A054-130+		
	CCT2S1/07	KE 103 A057-130+		
Cable Clamps Sets	CCU1C/AG	E3 102.248 + A	Cable Clamps Sets	
	CCU3C/CJ	E3 1031.2/6.2		
	CCU3C/CL	E3 1031.2/6.7		
	CCU4C/CK	E3 104.2/6.7+B		
	CCU4C/CN	E3 104.2/7.7+B		
	CCU4C/CQ	E3 104.2/8.7+B		
	CCU4C/AK	E3 104.3/6.7 + B		
	CCU4C/AN	E3 104.3/7.7 + B		
	CCU4C/AQ	E3 104.3/8.7 + B		
	CCV2C/AJ	E31 103.1/6.2 + B		
	CCV2C/AK	E31 103.1/6.7 + B		
	CCV2C/AJ	E31 103.2/6.2+B		
	CCV1C/CC	E31102.2/3.1+B		
	CCV1C/CD	E31102.2/3.6+B		
	CCV1C/CE	E31102.2/4.1+B		
	CCV1C/CF	E31102.2/4.3+B		
	CCV2C/CE	E31103.2/4.2+B		
	CCV2C/CG	E31103.2/4.7+B		
	CCV2C/CH	E31103.2/5.2+B		
	CCV2C/CI	E31103.2/5.7+B		
CCW1C/AC	E32 102.1/3.1 + A			
CCW1C/AD	E32 102.1/3.6 + A			
CCW1C/AE	E32 102.1/4.1 + A			
CCW1C/AF	E32 102.1/4.3 + A			