



Quality Products. Service Excellence.

100-240 VAC / 10A IEC Double Pole Switched Rackmount Outlet Strip 1582E DP

Series



Features

- On-Off switch is rocker type (double pole, single throw) with green light.
- Rated 100-240VAC, 10A, 50/60Hz
- Designed for power distribution on front or rear of unit with IEC power cords.
- 1U horizontal 19" rackmount installation.
- All steel housing with black powder coat finish.

Specifications

- Includes 10A circuit breakers to prevent accidental line overload.
- cULus listed to UL 60950-1 (2nd Edition); Amd1 + Amd2, and CAN/CSA C22.2 No. 60950-1-07 (2nd Edition); Amd1 + Amd2.
- TÜV certified to EN 60950-1:2006/A2:2013-09, and IEC 60950-1 (ed.2); am1;am2
- CE compliant to the European Low Voltage Directive 2014/35/EU.



Accessories

- Mounting Hardware
- Rail Depth Adapter Kit
- Input Accessory Cords

Part No.	Overall Dimensions			Number of Outlets		Outlet Type	Inlet Type	Inlet Location
	Height	Width	Depth	Front	Rear			
1582H8E1BKDP	1.72	19.00	2.66	8	0	C13	C14	Rear
1583H8E1BKDP	1.72	19.00	2.66	0	8	C13	C14	Rear

Data subject to change without notice

© 2018. Hammond Manufacturing Ltd. All rights reserved.

