



### Main

Range of product	Square D Pumptrol
Pressure sensor name	9013FS
Pressure sensor size	65 psi (5...45 psi)
Value of setting	30...50 psi
Electrical circuit type	Power circuit
Product specific application	Control electrically driven water pumps
Quantity per set	1
Type of packing	Individual

### Complementary

Pressure sensor type	Electromechanical pressure switch
Controlled fluid	Fresh water (-22...257 °F)
Adjustable range on rising pressure	20...65 psi
Approximate adjustable differential	15...30 psi
Destruction pressure	220 psi
Pressure actuator	Diaphragm
Pressure switch type of operation	Regulation between 2 thresholds
Scale type	Adjustable differential
Setting	Internal
Local display	Without
Contacts type and composition	2 NC, snap action, DPST-DB, Form YY
Cable entry number	2 0.88 in cable entries with 0.84 in across flats UL 508
Electrical connection	Screw-clamp terminals, clamping capacity: 10 AWG Screw-clamp terminals, clamping capacity: 5.261 mm <sup>2</sup>
Fluid connection type	0.25 inch NPSF internal conforming to UL 508
Short-circuit protection	20 A by cartridge fuse, type gG
Materials in contact with fluid	Zinc plated steel or equivalent flange Nitrile (Buna-N) or equivalent rubber diaphragm
Material	Polypropylene cover Noryl thermoplastic resin or equivalent cover
Operating position	Any position
Motor power kW	1.5 kW (2 hp) at 230 V AC, 1 phase 1.1 kW (1.5 hp) at 115 V AC, 1 phase 1.5 kW (2 hp) at 115 V AC, 3 phases 2.2 kW (3 hp) at 230 V AC, 3 phases 0.75 kW (1 hp) at 460 V AC, 3 phases 0.75 kW (1 hp) at 575 V AC, 3 phases 0.18 kW (0.25 hp) at 115 V DC 0.18 kW (0.25 hp) at 230 V DC
Electrical durability	100000 cycles at 10 cyc/mn
Mechanical durability	300000 cycles
Terminal block type	4 terminals
Operating rate	10 cyc/mn
[Ui] rated insulation voltage	575 V conforming to UL 508
Product weight	1 lb(US)
Repeat accuracy	+/- 3 %

Terminals description ISO n°1	L1-T1 L2-T2
Width	3.1 in
Height	2.8 in
Depth	3.76 in
Factory modification	Low pressure cut-off (AUTO-START-OFF) operates roughly 10 PSIG below cut-in

## Environment

Standards	CE UL 508 NSF ANSI 61 Annex G
Ambient air temperature for operation	-33...257 °F
Ambient air temperature for storage	-33...257 °F
Protective treatment	None
NEMA degree of protection	NEMA 1 conforming to UL 50
IP degree of protection	IP20 conforming to IEC 60529
Product certifications	UL listed file E12158 CSA file LR25490

## Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1150 - <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available <a href="#">Download Product Environmental</a>
Product end of life instructions	Available <a href="#">Download End Of Life Manual</a>