

64 32 120

Electronics End Cutting Nipper



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Sturdy, zero backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish (only finish 2) together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutting edges additionally induction hardened, cutting edge hardness at least 56 HRC
- High-grade special tool steel, forged, multi stage oil-hardened
 - Style:Oblique End Cutter, short head, with small bevel, $\alpha = 15^\circ$



Article No.	64 32 120
EAN	4003773017820
Head	mirror polished
Handles	with multi-component grips
Style	3
Cutting capacities medium hard wire (diameter) Ø mm	1,0
Cutting capacities hard wire (diameter) Ø mm	0,5
Cutting capacities soft wire (diameter) Ø mm	1,5
B mm	10,0
D mm	7,0
C mm	17,0
A mm	11,0
Dimensions angle °	15
Nominal size	120 mm
Length mm	120
Net weight g	92

technical change and errors excepted

