


25 01 140


Snipe Nose Side Cutting Pliers (Radio Pliers)



- Suitable for finer gripping and cutting work
- Half-round, long, tapered jaws
- Knurled gripping surfaces
- With cutting edges for soft, medium-hard and hard wire
- Cutting edges additionally induction hardened, cutting edge hardness approx. 61 HRC
- Vanadium electric steel, forged, multi stage oil-hardened



Article No.	25 01 140
EAN	4003773013082
Head	polished
Handles	plastic coated
Style	0
Pliers	black atramentized
Cutting capacities medium hard wire (diameter) Ø mm	2,5
Cutting capacities hard wire (diameter) Ø mm	1,6
T1 mm	8,0
W3 mm	15,0
W4 mm	2,5
T2 mm	2,0
L3 mm	42,0
Length mm	140
Net weight g	89



technical change and errors excepted

