




38 25 200 Mechanics' Pliers



- High bending strength of the pliers tips
- Gripping surfaces cross-hatched, knurled
- Vanadium electric steel; forged, oil-hardened
 - Style:40° bent jaws



Article No.	38 25 200
EAN	4003773043669
Pliers	chrome plated
Handles	with multi-component grips
Style	2
Head	
T1 mm	9,5
W3 mm	17,5
W4 mm	3,0
T2 mm	2,5
L3 mm	73,0
Dimensions angle °	40
Length mm	200
Net weight g	209



technical change and errors excepted

