

89 01 250

Water Pump Pliers with groove joint



- Easy, convenient engagement in 5 different positions due to milled tongue
- Self-locking on pipes and nuts: no slipping on the workpiece and low handforce required
- Non-slip joint
- Jaw profile designed to fit screws and nuts
- Joint design reduces strain of the centre bolt, hence no wear on pivot
- Guard prevents operators' fingers being pinched
- Gripping surfaces with special hardened teeth, teeth hardness approx. 61 HRC for tool length 250 mm: high wear resistance and stable gripping
- Chrome vanadium electric steel, forged, multi stage oil-hardened

Article No.	89 01 250
EAN	4003773013334
Pliers	black atramentized
Head	polished
Handles	plastic coated
Capacity for pipes, inches (diameter) Ø Inch	1 5/16
Capacities for nuts mm	36
Capacities for pipes (diameter) Ø mm	34
Length mm	250
Net weight g	340

technical change and errors excepted



Spare Parts

Article No.	EAN	
89 09 250 01	4003773053576	Joint screw for 89 01 250
89 09 250 02	4003773053583	Hexagonal nut for 89 01 250