

98 20 25

Screwdrivers for slotted screws



- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel



Article No.	98 20 25
EAN	4003773062325
Tip	burnished
Handle	insulating multi-component handle, VDE-tested
Insulation standard	IEC 60900 DIN EN 60900
Blade width mm	2,5
Blade length mm	75
Handle length mm	102
Blade thickness mm	0,4
Length of non-insulated blade mm	15
Length mm	177
Net weight g	32

technical change and errors excepted

