

98 20 30

Screwdrivers for slotted screws



- Ergonomically optimised dual component handle for fatigue reduced work and optimum transmission of force
- Handle design prevents rolling
- Chrome vanadium molybdenum steel



Article No.	98 20 30
EAN	4003773062332
Tip	burnished
Handle	insulating multi-component handle, VDE-tested
Insulation standard	IEC 60900 DIN EN 60900
Blade width mm	3,0
Blade length mm	100
Handle length mm	102
Nominal size	3,0 mm
Blade thickness mm	0,5
Length of non-insulated blade mm	15
Length mm	202
Net weight g	35

technical change and errors excepted

