

XZCP29P11L25

pre-wired connectors XZ - straight female -
M12 - 8 pins - cable PUR 25m



Main

Accessory / separate part category	Cabling accessory
Accessory / separate part type	Pre-wired connectors

Complementary

Electrical connection	M12, 8 pins straight female connector
Cable connector fixing	Screw-on
Collar material	Stainless steel 316L
Status LED	Without
Cable length	10 m
Cable outer diameter	5.2 mm
Cable composition	8 x 0.25 mm ²
Wire insulation material	PUR
[Ue] rated operational voltage	250 V AC 300 V DC
[In] rated current	2 A
Contact resistance	<= 5000 µOhm
Insulating resistance	>= 1 GΩ

Environment

IP degree of protection	IP67
Product certifications	CULus
Ambient air temperature for operation	-35...90 °C (static) -5...90 °C (flexing)
Ambient air temperature for storage	-35...100 °C

Offer Sustainability

Sustainable offer status	Not Green Premium product
--------------------------	---------------------------

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Connections and Schemes

Connectors



GY : Grey
PK : Pink
BU : Blue
WH : White
RD : Red
BN : Brown
GN : Green
YE : Yellow