# Product data sheet Characteristics

## ZC2JY41

# limit switch lever ZC2JY - thermoplastic offset roller lever variable length

Product availability: Stock - Normally stocked in distribution facility



Range of product	OsiSense XC	
Series name	Special format	
Product or component type	Limit switch lever	
Device short name	ZC2J	
Product compatibility	XC2J	
Associated head	ZC2JE01 ZC2JE02 ZC2JE03 ZC2JE04 ZC2JE05 ZC2JE06 ZC2JE07	; ;
Movement of operating head	Rotary	;
Type of operator	Roller lever spring return thermoplastic (variable length offset)	:
Type of approach	Lateral approach	

#### Complementary

Switch actuation	By 30° cam
Positive opening	Without

#### Environment

Ambient air temperature for operation	-40158 °F (-4070 °C) low temperature -13158 °F (-2570 °C) standard environment	
Ambient air temperature for storage	-40158 °F (-4070 °C) low temperature -40158 °F (-4070 °C) standard environment	
Environmental characteristic	Low temperature Standard environment	

#### Ordering and shipping details

Category	22449 - LIMIT SWITCHES,ACCESSORIES	
Discount Schedule	Т	
GTIN	00785901264262	<u>S</u>

Nbr. of units in pkg.	1	
Package weight(Lbs)	0.11	
Returnability	Υ	
Country of origin	FR	

### Offer Sustainability

Product end of life instructions	Need no specific recycling operations	·
	Reference not containing SVHC above the threshold	
REACh	Reference not containing SVHC above the threshold	
	Will not be compliant	
RoHS (date code: YYWW)	Will not be compliant	

### Contractual warranty

|--|