

ToLEDo GLS

ToLEDo GLS V3 470LM 827 B22 SL

0026674

Product features



PRODUCT OVERVIEW

Lamp finish	Frosted
Lamp shape	GLS
Colour temperature (K)	2700
CRI (Ra)	80
Dimmable	No
EAN code	5410288266749
Energy class	A+
Equivalent watt (W)	40
Cap/Base	B22
Type	ToLEDo GLS
Watt (Nominal) (W)	5
Light colour	Homelight
Ordering number	0026674
Efficacy (Rated) (lm/w)	94
Average life (h) - L70/B50	15000
Luminous flux (Rated) (lm)	470
Technology	LED
Voltage (V)	220-240
Colour consistency (SDCM)	6

DATA TABLE

General data

ToLEDo GLS

ToLEDo GLS V3 470LM 827 B22 SL

0026674

Average life (h) at Ta 25° C	15000
Control gear required	No
Lamp finish	Frosted
Lamp shape	GLS
Dimmable	No
Dry applications use only	Yes
EAN code	5410288266749
Energy class	A+
Energy saving lamp	Yes
General application	Hospitality; Residential & Consumer
Intended purpose	No
Cap/Base	B22
Lamp mercury content (mg)	0
Type	ToLEDo GLS
No. of switching cycles before premature failure (min)	50000
Optimal operating condition (°C)	25
Ordering number	0026674
Product name	ToLEDo GLS V3 470LM 827 B22 SL
Average life (h) - L70/B50	15000
Special purpose lamp	No
Starting time (max) (s)	0.05
Technology	LED
Transformer required	No
Warm-up time to 60% of full light (max) (s)	< 1s => 60%
E-number SE	8296522

Optical data

Colour temperature (K)	2700
CRI (Ra)	80
Light colour	Homelight
Lumen maintenance at end of nominal life (%)	70
Luminous flux (Nominal) (lm)	470
Luminous flux (Rated) (lm)	470
Suitable for accent lighting	No
Adjustable chromaticity	No
Colour consistency (SDCM)	6

Electrical data

Current (A)	36
Drive current (mA)	39
Equivalent watt (W)	40

ToLEDo GLS

ToLEDo GLS V3 470LM 827 B22 SL

0026674

kWh per 1000 hours burning time	5
Lamp power factor	0.5
Watt (Nominal) (W)	5
Efficacy (Rated) (lm/w)	94
Watt (Rated) (W)	5
Voltage (V)	220-240

Physical data

Max. Lamp Diameter (mm) - D	60
Lamp Length (mm) - C/L	107
Lamp dimension equal to filament lamp equivalent	Yes

