



Main

Range of product	OsiSense XS
Series name	Application
Sensor type	Inductive proximity sensor
Sensor name	XSP
Sensor design	Cylindrical M8
Body type	Fixed
Type of output signal	Discrete
[Us] rated supply voltage	12...48 V DC
IP degree of protection	IP67 conforming to IEC 60529

Complementary

Detection face	Frontal
Supply voltage limits	10...58 V DC
Residual current	<= 0.5 mA open state
Marking	CE

Environment

Product certifications	CCC
Ambient air temperature for operation	-13...158 °F (-25...70 °C)

Ordering and shipping details

Category	22486 - SENSORS, PROXIMITY
Discount Schedule	DS2
GTIN	00785901267140
Nbr. of units in pkg.	1
Package weight(Lbs)	0.12
Returnability	N
Country of origin	FR

Offer Sustainability

RoHS (date code: YYWW)	Will not be compliant
	Will not be compliant

Contractual warranty

Warranty period	18 months
-----------------	-----------
