

Product availability : Stock - Normally stocked in distribution facility



### Main

Product or component type	Single Throw Safety Switch
Line Rated Current	100 A
Product certifications	UL listed
NEMA degree of protection	NEMA 3R/12 galvanized steel
Device composition	None
Disconnecter device type	Fusible disconnect
Short-circuit current	10 kA H or K 200 kA R, J or L
Device mounting	Surface
Number of poles	3
Electrical connection	Lugs
Series name	Heavy duty
System Voltage	600 V AC/DC
AWG gauge	AWG 14...AWG 1/0 (copper) AWG 12...AWG 1/0 (aluminium)

### Ordering and shipping details

Category	00113 - H&HU SW,2&3P,N12,30-200A
Discount Schedule	DE1
GTIN	00785901482307
Nbr. of units in pkg.	1
Package weight(Lbs)	19.82
Returnability	Y
Country of origin	US

### Offer Sustainability

Sustainable offer status	Green Premium product
--------------------------	-----------------------

RoHS (date code: YYWW)	Compliant - since 1313 - Schneider Electric declaration of conformity <a href="#">Schneider Electric declaration of conformity</a>
REACH	Reference not containing SVHC above the threshold <a href="#">Reference not containing SVHC above the threshold</a>
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations

### Contractual warranty

Warranty period	18 months
-----------------	-----------