

40 Watt Hand-Grip Type Megaphone

With 3.5 mm Aux-in for iPod/MP3 Player Connectivity



Models: PMP43IN

QUICK GUIDE

FEATURES

- Dry Cell Operation
- Full ABS Body, Sturdy & Lightweight
- Built-in Siren & Microphone
- Clear Sound, Long Range & Efficient Design
- Conveniently Located Volume Controls & Switch
- Rechargeable Lithium Battery Included
- 3.5mm Aux-in for iPod/MP3 Player Connection

OPERATION

- Open the back cover by pressing down on the 'Open' Button
- Insert 6 x UM-1 Cells then close back cover until locks into position. Now, you're megaphone is ready for operation.
- To activate the megaphone, press the 'ON/OFF' button on the back cover.
- When using the megaphone, place your lips as close as possible to the megaphone when speaking. Adjust the 'Volume Control' to the desired level without causing any howling or feedback.
- Press the 'Music' button to activate soft music. Or press the 'Siren' button to activate emergency siren/alarm. To switch off the alarm, press the same button again, or press the 'ON/OFF' button.



PRECAUTIONS

Ensure correct polarity of cells used. Insert the batteries in the correct direction by aligning the (-) marks on the batteries with the spring in the back cover.

Use new batteries/cells whenever possible.

When the megaphone is not in use for a long period of time, remove the dry cells and replace.

Drained cells or rechargeable battery will not give sufficient sound volume.

SPECIFICATIONS:

- **Power Output:** 40 Watts
- **Voice Range:** 1,000 Yards
- **Power Source:** 6 x UM – 1 Cells (Not Included)
- **Battery Life:** 6 –8 Hours
- **Microphone:** Unidirectional
- **Dimensions:** Diameter: 8" x Length: 13 1/8"
- **Weight:** 2.20 LBS.

Design & Specifications subject to change without prior notice