



Overview

Model Name	APC Essential SurgeArrest 6 Outlet Wall Mount With USB, 120V
Includes	USB Power Adapter , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Aruba , Bahamas , Barbados , Belize , Bermuda , Canada , Colombia , Costa Rica , Cuba , Dominican Republic , Ecuador , El Salvador , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Puerto Rico , Trinidad And Tobago , Turks And Caicos Islands , United States , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Number of Outlets	4
Receptacle Style	NEMA 5-15R

Input

Nominal Input Voltage	120V
Input Power	1200 W
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	NEMA 5-15P
Maximum Line Current per phase	15.0 A
Maximum Input Current	15 A

Surge Protection and Filtering

Surge energy rating	1080 joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	40.0 dB
Peak Current Normal Mode	60 (/PH) kA
Peak Current Common Mode	72.0 kA
NM Surge Response Time (ns)	1.0 ns

Physical

Net Weight	0.25 kg
Maximum Height	102.0 mm

Maximum Width	38.0 mm
Maximum Depth	140.0 mm
Shipping Weight	0.26 kg
Shipping Height	241.0 mm
Shipping Width	57.0 mm
Shipping Depth	197.0 mm
Master Carton Units	6.0
Master Carton Dimensions (Length x Width x Height)	13.4 x 8.4 x 10 inches
Master Carton Weight	2.27 kg
SCC Codes	1073130433182 4
Color	Beige
Units per Pallet	504.0

Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

Conformance

Approvals	ETL
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$50000
UL 1449 TVSS Rating	400

Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs