

PVX™ 15



OVERVIEW

The PVX 15 passive loudspeakers deliver superior sound quality by utilizing advanced materials like its lightweight, roadworthy molded polypropylene exterior. Lightweight, durable and voiced for live music or speech applications, these two-way speaker systems will handle 400 watts program and 800 watts peak power and feature heavy-duty woofers, 2-3/8" voice coils and the Peavey RX14™ 1.4-" titanium diaphragm compression driver coupled to a constant directivity horn.

FEATURES

- 400 watts program
- 800 watts peak
- Top, bottom and right side flying point inserts
- Full-coverage heavy-duty perforated steel grille, with powder-coat finish
- Rugged Construction
- Patented, asymmetrical Quadratic Throat
- Waveguide™ Technology - 100° by 50° coverage. 15° upward and 35° downward directing sound to your audience
- RX14™ - Titanium Compression Driver
- Weight Unpacked: 47.00 lb(21.319 kg)
- Weight Packed: 53.79 lb(24.4 kg)
- Width Packed: 21.625"(54.9275 cm)
- Height Packed: 31.625"(80.3275 cm)
- Depth Packed: 20.375"(51.7525 cm)