

## 4 and 8 PoE Port 10/100 802.3af/at Switches

**POE4SW6** 4 PoE ports

**POE8SW9** 8 PoE ports

### Features

- Power IP cameras via Power over Ethernet
- Ethernet speed up to 10/100MBPS
- Meets IEEE 802.3af/at Ethernet standard
- 4 or 8 PoE ports with uplink
- 2 year warranty



POE4SW6



POE8SW9

### Specifications

Total Ports .....	6 (POE4SW6)
	9 (POE8SW9)
PoE Ports .....	4 (POE4SW6)
	8 (POE8SW9)
Ethernet Speed.....	10/100MBPS
Ethernet Standards.....	IEEE 802.3/802.3u/802.3at/af
Single Port Max Power.....	25W
Entire Unit Max Power.....	65W (POE4SW6)
	100W (POE8SW9)
Operating Temperature.....	32° F – 131° F
Storage Temperature.....	-40° F – 185° F
Operating Humidity.....	0% – 95%
Dimensions.....	5.3" (W) x 1" (H) x 3.4" (L) (POE4SW6)
	8" (W) x 1" (H) x 4" (L) (POE8SW9)
Weight .....	12.4 oz. (POE4SW6)
	1.1 lbs. (POE8SW9)