

## 802.3af/at PoE Splitter

### POESPL

#### Features

- Power non-POE IP cameras via a PoE signal by splitting the signal into Ethernet and power
- POESPL can handle up to 20W 802.3at PoE power
- Ethernet speed up to 10/100MBPS
- 2 year warranty



#### Specifications

Ports ..... 1 x RJ-45, 1 x 2-pin terminal block output, 1 x RJ-45 input  
Ethernet Speed.....Up to 10/100MBPS  
PoE Standards .....IEEE 802.3at/af  
PoE Power.....20W Max  
Input Power .....PoE 36V – 57V  
Output Power.....12VDC  
Operating Temperature...32° F – 131° F  
Storage Temperature.....-40° F – 185° F  
Operating Humidity.....0% – 95%  
Dimensions.....4.7" (W) x 2.4" (H) x 1.5" (L)  
Weight .....8 oz.