

# P8V

## APC Premium Audio/Video Surge Protector 8 Outlet with Coax Protection, 120V



### Overview

Model Name	APC Premium Audio/Video Surge Protector 8 Outlet with Coax Protection, 120V
Includes	6ft Gold Plated Coaxial Cable , 6ft High speed internet cable
Standard Lead Time	Usually in Stock
Product Distribution	Canada , Mexico , United States

### Output

Number of Outlets	8
Receptacle Style	NEMA 5-15R

### Input

Nominal Input Voltage	120V
Input Power	0 W
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	NEMA 5-15P
Maximum Line Current per phase	15.0 A
Cord Length	1.83 meters
Maximum Input Current	0 A

### Surge Protection and Filtering

Surge energy rating	4720 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	70.0 dB
Peak Current Normal Mode	20 kA
Peak Current Common Mode	40.0 kA
NM Surge Response Time (ns)	1.0 NS
Data Line Protection	Cable modem / Video protection
Data Lines Protected (multi-line only)	1
Let Through Voltage Rating	330

### Physical

Net Weight	0.95 kg
Maximum Height	394.0 mm
Maximum Width	95.0 mm
Maximum Depth	51.0 mm
Shipping Weight	1.23 kg
Shipping Height	450.0 mm
Shipping Width	180.0 mm
Shipping Depth	60.0 mm
Master Carton Units	12.0
Master Carton Dimensions (Length x Width x Height)	20 x 11 x 24 inches
Master Carton Weight	15.91 kg

Color	Black
Units per Pallet	384.0

### Environmental

Operating Environment	0 - 40 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-15000 meters
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

### Conformance

Approvals	CSA , UL 1363 , UL 1449
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$100000
UL 1449 TVSS Rating	330

### Sustainable Offer Status

RoHS	Compliant
------	-----------