

Stage 200

Dual-Channel Handheld VHF Wireless System

 WIRELESS



POSITIONING

Samson's Stage 200 is a dual-channel wireless microphone system that provides two handheld dynamic microphones that transmit to a single rugged metal receiver. Each handheld features Samson's Q6 mic element, providing crisp, clear sound and reliable VHF wireless performance for home karaoke, live presentation, education, house of worship and other dual-performer applications.

FEATURES

VHF Operation

The Stage 200 operates in the reliable VHF frequency spectrum, which has become significantly less crowded with the advancement of digital TV. VHF operation also provides both mic transmitters with an exceptional battery life of up to 10 hours via two AA batteries (not included).

Versatile Performance

Featuring the rugged metal SR200 receiver, the Stage 200 is designed for maximum durability and versatility. Its back panel provides two 1/4" outputs, as well as a balanced XLR out, to connect to a dedicated mixer or powered PA speaker. The 1/4" outputs send each channel separately, while the XLR sends a mix of both. Front panel volume controls on each channel let you find the perfect blend between two performers.

Simple Setup

Samson has been dedicated to driving wireless innovation, always striving to make it easier for performers everywhere to cut the chord. The Stage 200's fixed frequency operation provides instant setup. Simply plug in the receiver and turn on your transmitters to experience quality wireless performance. A 200' operating range provides ample freedom for any presenter or performer duo.

APPLICATIONS

- Karaoke
- Education/corporate AV
- Wedding DJs and performers
- House of worship

SPECIFICATIONS

Stage 200 Wireless System

Working Range..... 200' (100m) line of sight
 Dynamic Range..... >103dB A-weighted
 Signal To Noise >90dB

SR200 Wireless Receiver

Audio Output Level Balanced +9dBu, unbalanced +14dBu
 Audio Output Impedance Balanced 240Ω, unbalanced 810Ω

VH200 Handheld Transmitters

Microphone Element Samson Q6 dynamic
 Pickup Pattern Cardioid
 RF Power 10 mW EIRP
 Battery Life..... 10 hours from 2 x AA batteries
 Accessories..... AC adapter

Gift Box Dimensions 11.25" x 16.25" x 2.5"
 (286mm x 412mm x 65mm)

Gift Box Weight..... TBD

Master Carton Quantity TBD

UPC (US only)..... 809164217374 (Channel A)
 809164217381 (Channel B)
 809164217398 (Channel C)
 809164217404 (Channel D)

SKU (US only)..... SWS200HH-A
 SWS200HH-B
 SWS200HH-C
 SWS200HH-D