

# MA0625SIM-3PIN -

FAN, 60MM, 3 PIN



6CM FAN - 3 PIN

Fan Size: 60mm x 60mm

Current Type: DC

External Diameter: 60mm

External Height: 60mm

Flow Rate - Imperial: 23.72cu.ft/min

Flow Rate - Metric: 0.66m<sup>3</sup>/min

Noise Figure Typ: 32dB

Power Consumption: 2.4W

Speed Range Max: 4500rpm

Supply Voltage: 12V

Supply Voltage V DC: 12V