

Bosch GSS 280 A Professional



Technical data: GSS 280 A Professional

Rated power input	330 W
No-load speed	11000 rpm
No-load orbital stroke rate	22000 opm
Oscillating circuit diameter	2.4 mm
Weight without cable	2.6 kg
Sanding surface	
Sanding plate, width	114 mm
Sanding plate, length	226 mm
Sanding sheet for clamping, width	115 mm
Sanding sheet for clamping, length	280 mm
Sanding sheet with Velcro-type fastening, width	115 mm
Sanding sheet with Velcro-type fastening, length	230 mm



Dust extraction

Directly into the integral dust bag on the machine and/or using an all-purpose dust extractor.

Features: GSS 280 A Professional

- Frontal flush sanding possible thanks to removable auxiliary handle
- High sanding performance
- Bosch Micro-filter System: perfect mobile extraction
- Also suitable for left-handers